



Improving your PERFORMANCE

323Du/RL and 323Du/RL2 RS232/analogue/manual control high flow pumps


Caratteristiche


- RS232 serial communication
- High-performance microprocessor controlled pumps
- Single channel flow rates from 0.06ml/min to 2200ml/min
- Precision digital speed control 220 steps from 1.5 to 200rpm, 147:1 control ratio
- Digital TTL or remote switch inputs for run/stop and direction
- Rear panel 25D socket accepts analogue auto-control signal input for speed control 4-20mA, 0-10V
- High visibility digital display and keypad lock
- Compact design, chemical resistant case, contemporary styling
- Zero maintenance, quiet brushless DC motor
- Rapid and simple tube loading 501RL pumphead accepts seven tube bore sizes.
- For higher suction, viscosity or delivery pressure operation, order 501RL2 pumphead which accepts 2.4mm wall thickness tubing
- MemoDose facility for accurate single shot dosing
- Auto-restart for mains failure recovery and timer control



Portate (ml/min)

	Velocità rpm	Diametro tubo e portate (ml/min)						
		0.5mm	0.8mm	1.6mm	3.2mm	4.8mm	6.4mm	8.0mm
323Du/RL	1.5-220	0.06-9.2	0.18-27	0.84-94	2.8-410	6.1-890	9.5-1400	15-2200





323Du/RL and 323Du/RL2 RS232/ analogue/manual control high flow pumps

Codici		
323Du/RL 1.5-220rpm	drive + 501RL pumphead for 1.6mm wall tube	030.3152.RL0*
323U 1.5-220rpm	drive only	036.3152.000*
501RL	pumphead for 1.6mm wall tube	053.0001.L00
501RL2	pumphead for 2.4mm wall tube	053.0001.L20

*Sostituire l'ultimo **0** con **A**, **E** o **U** per rete elettrica **americana**, **europea** o **britannica**

If required for use with STA-PURE and Chem-Sure tubing, please contact Watson-Marlow Bredel technical support for drive and pumphead selection.

Codici per tubi per teste 501RL				
Diam. (mm)	Bioprene	Marprene	Platino Silicone	PVC
0.5 / 1.6	903.0005.016	902.0005.016	913.A005.016	
0.8 / 1.6	903.0008.016	902.0008.016	913.A008.016	
1.6 / 1.6	903.0016.016	902.0016.016	913.A016.016	950.0016.016
3.2 / 1.6	903.0032.016	902.0032.016	913.A032.016	950.0032.016
4.8 / 1.6	903.0048.016	902.0048.016	913.A048.016	950.0048.016
6.4 / 1.6	903.0064.016	902.0064.016	913.A064.016	950.0064.016
8.0 / 1.6	903.0080.016	902.0080.016	913.A080.016	950.0080.016
1.6 / 2.4	903.0016.024	902.0016.024	913.A016.024	
3.2 / 2.4	903.0032.024	902.0032.024	913.A032.024	
4.8 / 2.4	903.0048.024	902.0048.024	913.A048.024	
6.4 / 2.4	903.0064.024	902.0064.024	913.A064.024	
8.0 / 2.4	903.0080.024	902.0080.024	913.A080.024	
Diam. (mm)	Neoprene	STA-PURE®	Chem-Sure®	Fluorel®
0.8 / 1.6	920.0008.016			970.0008.016
1.6 / 1.6	920.0016.016	960.0016.016	965.0016.016	970.0016.016
3.2 / 1.6	920.0032.016	960.0032.016	965.0032.016	970.0032.016
4.8 / 1.6	920.0048.016	960.0048.016	965.0048.016	970.0048.016
6.4 / 1.6	920.0064.016	960.0064.016	965.0064.016	970.0064.016
8.0 / 1.6	920.0080.016	960.0080.016	965.0080.016	970.0080.016
1.6 / 2.4		960.0016.024	965.0016.024	
3.2 / 2.4		960.0032.024	965.0032.024	
4.8 / 2.4		960.0048.024	965.0048.024	
6.4 / 2.4		960.0064.024	965.0064.024	
8.0 / 2.4		960.0080.024	965.0080.024	

® Fluorel è un marchio registrato da Dyneon LLC, 3M Hoechst Enterprise

® STA-PURE o Chem-Sure è una marchio registrato da W.L Gore & Associates Inc.
Please state the product code when ordering pumps and tubing.

Specifiche

Peso	5.6kg
Dimensions	H132 x W230 x L225
Control ratio	147:1
Standards	CE, IEC335-1, EN60529 (IP31)
Alimentazione	1ph, 100-120V, 220-240V 50/60Hz, 100VA

Ta

Drive	
Drive base	Powder coated aluminium casting
Drive top	Self-coloured ABS plastic
Pumphead	
Rotor	Mazak, chromium plated
Tube clamps, hinges	Acetal copolymer - kematal
Guide rollers	Delrin
Rollers	MoS2 filled Nylon 6 (Nylatron)
Guard	Polycarbonate
Springs, spindles	Stainless steel



Watson-Marlow-Bredel Pumps
Falmouth
Cornwall
England
TR11 4RU
Tel: +44 (0) 1326 370370
Fax: +44 (0) 1326 376009
www.watson-marlow.com
Email support4gb@watson-marlow.co.uk